

Angular milling cutter HSSE Co 5


ORION[®]

Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

Execution:

- Straight-grooved
- Finely toothed
- Straight shank according to DIN 1835 B.
- For cutting on periphery and end face



Art. no.	15814 055
Brand	ORION
Manufacturer Part Number	15814055
Cutting material	HSSE Co5
Type	N
Number of cutting edges	12 PCS
Chamfer angle	45 Degree
Tool holding device	HB parallel shank
Cutting edge diameter	32 mm
Width of cutting edge	8 mm
Immersion depth	23 mm
Length	71 mm
Shank diameter	16 mm
Form	C
fz steel 700	0.08 mm
Gross Weight	0.100 kg
Product Group	106

EAN

4039247098101