


## Pneumatic angle drill MD-3312B

Angled version



### Execution:

- Anti-clockwise and clockwise rotation
- Noise-dampened air outlet with handle



<b>Art. no.</b>	<b>75066 106</b>
<b>Brand</b>	TOKU
<b>Manufacturer Part Number</b>	MD-3312B
<b>Model</b>	MD-3312B
<b>Max. drilling diameter in steel</b>	10 mm
<b>Max. idle speed</b>	1900 rpm
<b>Power rating</b>	380 W
<b>Air consumption</b>	6 l/s
<b>Min./max. drill chuck span width</b>	1-10 mm
<b>Inner hose diameter</b>	6.5 mm
<b>Weight</b>	0.91 kg
<b>With right/left-hand rotation</b>	Yes
<b>Operating pressure</b>	6.3 bar
<b>Length</b>	205 mm
<b>Sound-pressure level</b>	77 dB
<b>Gross Weight</b>	0.956 kg
<b>Product Group</b>	7AE

### EAN

8717981000111