

## Product information


# 97 52 35

## KNIPEX PreciForce® Crimping Pliers

- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened



General	
Article No.	97 52 35
EAN	4003773051886
Pliers	burnished
Handles	with multi-component grips
Weight	494 g
Dimensions	220 x 60 x 31 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details	
	
Application	non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)
Capacity in square millimetres	0.5 — 6.0 mm <sup>2</sup>
Number of crimping positions	3
AWG	20 — 10

*technical change and errors excepted*