

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0154660610](#)
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 0.50mm Pitch Premo-Flex FFC Jumper with Latching Ears, Same Side Contacts (Type A), 152.00mm Cable Length, Tin (Sn) Plating, 10 Circuits

Documents:

Drawing (PDF)	Datasheet (PDF)
Product Specification 154660001-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Cable
Series	15466
Crimp Quality Equipment	Yes
Overview	FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Product Name	Premo-Flex FFC Jumper
Taxonomy	Flexible Printed Circuit (FPC)
UPC	196823196195

Physical

Cable Length	152.00mm
Circuits (Loaded)	10
Contact Layout Type	A (same side)
Material - Plating Mating	Tin
Net Weight	0.499/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

Material Info

Reference - Drawing Numbers

Product Specification	154660001-000
Sales Drawing	154660001-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15466 Series](#)

Mates With

Easy-On FFC/FPC Connector [505278](#)