

Pneumatic grease gun with high-pressure hose and hydraulic nosepiece

Model DFP 1000, for use with loose grease



Application:

For simple lubrication, can be filled with loose grease.

Execution:

- Single-handed operation
- Pressure ratio 1:60
- Max. operating pressure: 420 bar
- Input pressure: min. 2 to max. 7 bar
- Recommended air pressure: 6 bar
- With 300-mm high-pressure hose and hydraulic nose piece
- Nozzle pipe or high-pressure hose connection: M10x1

Advantage:

- With 150-mm nozzle tube, even hard-to-reach lubrication areas are easy to access



Art. no.	56266 020
Brand	SAMOA-HALLBAUER
Manufacturer Part Number	10210
Volumetric capacity	1 l
Connection thread	MT G 1/8 inch
Feed volume per stroke	1 cm ³
Gross Weight	2.500 kg
Product Group	5IG

EAN

4024937102107