

Data Sheet

Fujitsu Display L22T-7 LED

All-round display: 54.6 cm (21.5-inch) widescreen
Ease of use

The Fujitsu Display L22T-7 LED comes in a 16:9 format with a trendy style. There is no compromise in picture quality and energy efficiency. It is the best choice to get Full HD resolution with reduced office desk space. It is easy-to-use and once it is installed you never have to adjust it again - proven Fujitsu quality.

Environment-friendly LED technology

1920 x 1080 high resolution for pin sharp pictures with modern 16:9 format applications

Proven eco-friendliness with ENERGY STAR® 6.0

Ease of use display for home and office, high pixel density application

Due to integrated speaker no further accessories needed



Technical details

Special features

LED backlight panel, Keep aspect ratio option

Stand details

Stand	removable
Picture height over desk (min)	81 mm
Tilt angle	-3° / +20°

Picture performance

Panel and backlit	TN/LED
Screen Surface Treatment	Anti-glare, 3H hard coating
Contrast - typical	1,000:1
Contrast - advanced	20,000,000:1
Response time typical	5 ms
Viewing angle (h/v) - typical	176°/170° CR5:1
Color performance	16.7 million colors (Hi-FRC)
Brightness - typical	250 cd/m ²

Size and resolution

Aspect ratio	16:9
Diagonal Size	54.6 cm (21.5-inch)
Resolution (native)	1920 x 1080 pixel (recommended)
Resolution (interpolated)	1680 x 1050 pixel, 1600 x 1200 pixel, 1440 x 900 pixel, 1360 x 768 pixel, 1280 x 1024 pixel, 1152 x 870 pixel, 1024 x 768 pixel, 800 x 600 pixel, 720 x 400 pixel, 640 x 480 pixel
Video modes	1080i/p, 720i/p, 576i/p, 480i/p
Picture size	476.6 mm x 268.1 mm
Pixel Pitch	0.248 mm

Frequencies

Horizontal	31 kHz to 83 kHz
Horizontal analog	180 Mhz
Horizontal digital	165 Mhz
Vertical	55 - 76 Hz

Connectivity

DVI	1 x DVI (HDCP)
VGA/D-SUB	1 x D-SUB
Audio signal output	3.5 mm stereo phone jack
Audio signal input	3.5 mm stereo phone jack
Audio sound output	2 x 1.5 W

OSD Languages and setting options

Languages	English, French, German, Italian, Polish, Spanish, Dutch, Russian, Japanese, Chinese simply
Brightness / Contrast	Brightness, Contrast
Color	6500K, 7500K, 9300K, Custom Color
Image adjust	H-Position, V-Position, Clock, Phase, Sharpness
Audio	Mute, Volume
Information	Resolution, V-freq
Setup	Input select, Language, OSD-Timeout, Factory recall

Power consumption (typical, w/o sound)

Soft switch off	0.11 W
Power save mode	0.14 W
Operating with EPA settings	16.2 W
Operating maximum brightness	21 W
Power supply display	integrated
Power notes	without sound

Electrical values

Rated voltage range	100 V - 240 V
Rated frequency range	50 Hz - 60 Hz
Protection class	1

Compliance

Europe	CE certification according to EC Directive 2004/108/EEC, EN 60950, RoHS, WEEE, IT-Eco-Declaration
Model	W2112
Russia	EAC
USA/Canada	FCC Class B, cUL
Saudi Arabia	SASO
Global	TCO Displays 6.0, ENERGY STAR® 6.0, EPEAT® Silver (dedicated regions), ISO9241-307 (Pixel fault class II)
Compliance link	http://globalsp.ts.fujitsu.com/sites/certificates

Quality and Reliability

MTBF (demonstrated)	60.000 h
---------------------	----------

Dimensions / Weight / Environmental

Dimension without stand (W x D x H)	514.7 x 54.6 x 322.1 mm 20.26 x 2.15 x 12.68 inch
Dimension with stand (W x D x H)	514.7 x 177.7 x 369.6 mm 20.26 inch x 7.0 x 14.55 inch
Weight (packed)	4.5 kg 9.92 lbs
Weight (unpacked)	2.9 kg 6.39 lbs
Weight (Monitor only)	2.65 kg 5.84 lbs
Operating ambient temperature	5 - 35 °C (41 - 95 °F)

Miscellaneous

Miscellaneous	VESA DDC/ CI, Flat Display Mounting Interface VESA MIS-D 100 C, Kensington lock
Color	Piano black

Package content

Display delivered accessories	Power cable for wall socket (Euro-Schuko-Type CEE7) 1.5 m, D-SUB Data cable 1.5 m, Audio cable 1.5 m, Safety booklet, Warranty booklet, Quickstart flyer, Utility CD
Display delivered accessories notes	Data cables and audio cable detachable on display

Order information

Order Code	S26361-K1528-V160
Country specific order code	BDL:K1528V160-UK - with UK power cable, mandatory for Arabian countries
EAN Code	4053026557504

Warranty

Standard Warranty	3 years (depending on country)
Service level	Collect & Return Service (depending on country specific requirements) (depending on country)
Warranty Terms & Conditions	http://support.ts.fujitsu.com/warranty
Spare Parts availability	3 years after end of product life
Service Weblink	http://www.fujitsu.com/fts/services/support

More information

Fujitsu OPTIMIZATION Services

In addition to Fujitsu Display L22T-7 LED, Fujitsu provides a range of platform solutions. They combine reliable Fujitsu products with the best in services, know-how and worldwide partnerships.

Fujitsu Portfolio

Build on industry standards, Fujitsu offers a full portfolio of IT hardware and software products, services, solutions and cloud offering, ranging from clients to datacenter solutions and includes the broad stack of Business Solutions, as well as the full stack of Cloud offering. This allows customers to leverage from alternative sourcing and delivery models to increase their business agility and to improve their IT operation's reliability.

Computing Products

www.fujitsu.com/global/services/computing/

Software

www.fujitsu.com/software/

More information

Learn more about Fujitsu Display L22T-7 LED, please contact your Fujitsu sales representative or Fujitsu Business partner, or visit our website.
<http://www.fujitsu.com/fts/displays>

Fujitsu green policy innovation

Fujitsu Green Policy Innovation is our worldwide project for reducing burdens on the environment. Using our global know-how, we aim to contribute to the creation of a sustainable environment for future generations through IT. Please find further information at <http://www.fujitsu.com/global/about/environment/>



Copyrights

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded.

Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

For further information see www.fujitsu.com/terms

Copyright © Fujitsu Technology Solutions

Disclaimer

Technical data are subject to modification and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner.

Contact

FUJITSU Technology Solutions
Website: www.fujitsu.com/fts
2014-01-13 CE-EN

All rights reserved, including intellectual property rights. Technical data subject to modifications and delivery subject to availability. Any liability that the data and illustrations are complete, actual or correct is excluded. Designations may be trademarks and/or copyrights of the respective manufacturer, the use of which by third parties for their own purposes may infringe the rights of such owner. For further information see www.fujitsu.com/terms
Copyright © Fujitsu Technology Solutions