

MSVD POWER SOCKET NEMA

Mounting rail

USA (2 × NEMA 5-20)


Screw terminals

LED (yellow)

Each socket can be loaded with 20 A, however, the total load of both sockets must be below 30 A.

[Link to Product](#)

Illustration



Product may differ from Image

Approvals

The information in this brochure has been compiled with the utmost care.
Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15



Technical Data

Operating voltage	max. 125 V AC
Operating current	max. 20 A

General data

Mounting method	DIN-rail mountable (EN 60715)
Connection	Screw terminals: max. 6 mm ²
Dimensions H × W × D	126×64×55 mm

Commercial data

country of origin	CZ
customs tariff number	85369010
minimum order quantity	1