



Datenblatt - Fiche technique - Data sheet

21.15.8705



ROLINE LWL-Kabel 50/125 μ m OM3, LC/LC, türkis, 5m

ROLINE Câble FO 50/125 μ m, LC/LC, OM3, turquoise, 5m

ROLINE Fibre Optic Jumper Cable, 50/125 μ m, LC/LC, OM3, turquoise, 5 m

1 2 3 4 5 6

A

A


B

B

C

C

D



Specification:

- 1. Connector Type : LC Multimode
- 2. Cable Type :
 2-1 Zipcord Cable, ϕ 2.0mm, 50/125um Multimode.(OM3 Corning Fiber)
 2-2 Calbe Jacket : Aqua Color, PVC Material.
- 3. Cable Marker
- 4. Shrink Tube
- 5. Length : xM(FT)

Performance:

- a. Insertion Loss : <0.5 dB
- b. Fiber Extention : $-0.05\mu\text{m} < H < +0.05\mu\text{m}$
- c. ϕ 1.25mm Ferrule End-face Radius : $7 < R < 25\text{mm}$
- d. Apex Offset : < 50um
- e. Increase in insertion loss after 500 mating : 0.2 dB Max
- f. Operating Temperature : -20° to $+70^{\circ}$
- g. Storage Temperature : -40° to $+80^{\circ}$

Remack#

21.15.8700	MultiMode, LC-LC,50/125 um	0.5M
21.15.8701	MultiMode, LC-LC,50/125 um	1M
21.15.8702	MultiMode, LC-LC,50/125 um	2M
21.15.8703	MultiMode, LC-LC,50/125 um	3M
21.15.8705	MultiMode, LC-LC,50/125 um	5M
21.15.8708	MultiMode, LC-LC,50/125 um	10M

GENERAL TOLERANCE OF DIMENSIONS X.XXX ±0.005 X.XX ±0.05 X.X ±0.1	DRAWING	07.JAN.2011	Abby	Rotronic Co.,Ltd.
	CHECK	07.JAN.2011	MAER	
	APPROVAL	07.JAN.2011	YTY	
		DATE	NAME	ITEM NO.: 21.15.XXXX 有吊卡
SCALE	1/1 (A4)	UNIT	mm	DES.: LC to LC Duplex patch cord
	DRAWING NO.	SFNIE503131xxxx03001(SA1)		A1
	DRAWING CLASSIFICATION	S	SHEET 1 OF 1	

1 2 3 4 5 6

10cm