

Shelf trolley with three load areas, load capacity 250 kg

Load area 900 x 315 mm and 1240 x 415 mm

fetra[®]
Transportgeräte

Application:

For the transportation and serving of small parts or other materials in Euro boxes.

Version:

- Steel tube/profile steel welded
- Variable screw-in shelves, 100 mm grid
- Steel frame with inserted wooden plate, surface beech decor, edge 12 mm high
- Infinitely adjustable inclination from 0° to 35°, secure locking by
- means of gripping screws

Art. no.	50268 424
Load-carrying capacity	250 kg
Loading surface size	900 x 315 mm
Loading surface length	900 mm
Loading-surface width	315 mm
Length	1050 mm
Width	362 mm
Height	1205 mm
Length x width x height	1050 x 362 x 1205 mm
Loading-surface height	370 mm
Loading-surface height 2	670 mm
Loading-surface height 3	970 mm
Wheel diameter	125 mm
Material of wheel	TPE
Wheel width	32 mm
Total stop optional	No



EAN-Code

4017976028811