

USB, Ausführung A, Side-Entry, Ultraflach

USB, version A, Side-Entry, ultra flat



SMT



DIP

Isolierkörper

Nylon PA9T

Kontakte

Phosphorbronze, t=0.25mm

Gehäuse

Messing t=0.3mm
Oberfläche: Vernickelt

Durchschlagsspannung

500V AC (1min)

Isolationswiderstand

1000MΩ min.

Nennspannung und Strom

1.5A bei 250V AC minimum

Insulator

Nylon PA9T

Contacts

Phosphorbronze, t=0.25mm

Shell

Brass t=0.3
Finish: Nickel Plated

Withstanding voltage


500V AC (1min)

Insulation resistance


1000MΩ min.

Rated voltage and current





1.5A at 250V AC minimum



DIP



SMT



Bestellcode : **A - USB - A - x**
Ordercode :

Bitte „x“ durch die unten geeignete Optionen ersetzen
Please replace „x“ with appropriate options listed below

1.

Ausführung
LP -DIP
LP/SMT -SMT

Version
LP -DIP
LP/SMT -SMT

1.

D-Sub / Hoods
Centronics

Multiflex

Modular

USB

Switches

Powercords
Powersockets

MiniDIN

DIN4161x
Hardmetric

Sockets + Strips
Jumper