

J.10 J - 3/8" metric 12-point sockets



Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.

A [mm]:	10
d [mm]:	17,6
d1 [mm]:	14,7
L [mm]:	27
L1 [mm]:	7,8
12-Point [mm]:	12
[g]:	26

