

MOSA M8 MALE 0° FIELD WIREABLE (IDC)

4-pol. 0.25...0.5mm²

Male straight


4-pole

Insulation displacement technology


Connection cross section: 0.25...0.5 mm²

[Link to Product](#)

Illustration



Male



Product may differ from Image

Approvals



Form

08341

Technical Data

Operating voltage	max. 32 V AC/DC
Operating current per contact	max. 4 A
Connection cross section	0.25...0.5 mm² (conductor diameter min. 0.1 mm)
Sealing range (cable diameter)	4...5.1 mm
Wire isolation	PVC, PP, TPE
Outer wire diameter	1.2...1.6 mm
Protection	IP67 inserted and tightened (EN 60529)

General data

Temperature range	-25...+85 °C
Dimensions H × W × D	53×13×13 mm

Commercial data

country of origin	DE
customs tariff number	85369010

minimum order quantity

1