

## Angular milling cutter HSSE Co 5


**ORION**<sup>®</sup>

### Application:

For milling ducts and other angular geometries in tool and mechanical engineering.

### Execution:

- Straight-grooved
- Finely toothed
- Straight shank according to DIN 1835 B.
- For cutting on periphery and end face



<b>Art. no.</b>	<b>15814 140</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	15814140
<b>Cutting material</b>	HSSE Co5
<b>Type</b>	N
<b>Number of cutting edges</b>	10 PCS
<b>Chamfer angle</b>	60 Degree
<b>Tool holding device</b>	HB parallel shank
<b>Cutting edge diameter</b>	25 mm
<b>Width of cutting edge</b>	10 mm
<b>Immersion depth</b>	22 mm
<b>Length</b>	67 mm
<b>Shank diameter</b>	12 mm
<b>Form</b>	C
<b>fz steel 700</b>	0.06 mm
<b>Gross Weight</b>	0.072 kg
<b>Product Group</b>	106

### EAN

4039247098132