

## Shelf trolley with three load areas, load capacity 250 kg

Load area 900 x 315 mm and 1240 x 415 mm

fetra<sup>®</sup>  
Transportgeräte

### Application:

For the transportation and serving of small parts or other materials in Euro boxes.

### Version:

- Steel tube/profile steel welded
- Variable screw-in shelves, 100 mm grid
- Steel frame with inserted wooden plate, surface beech decor, edge 12 mm high
- Infinitely adjustable inclination from 0° to 35°, secure locking by
- means of gripping screws

<b>Art. no.</b>	<b>50268 429</b>
<b>Load-carrying capacity</b>	250 kg
<b>Loading surface size</b>	1240 x 415 mm
<b>Loading surface length</b>	1240 mm
<b>Loading-surface width</b>	415 mm
<b>Length</b>	1355 mm
<b>Width</b>	477 mm
<b>Height</b>	1197 mm
<b>Length x width x height</b>	1355 x 477 x 1197 mm
<b>Loading-surface height</b>	370 mm
<b>Loading-surface height 2</b>	670 mm
<b>Loading-surface height 3</b>	970 mm
<b>Wheel diameter</b>	125 mm
<b>Material of wheel</b>	TPE
<b>Wheel width</b>	32 mm
<b>Total stop optional</b>	No



### EAN-Code

4017976328836