

## BSW 506 pneumatic countersink drill bit

Angled design

MANNESMANN  
DEMAG

### Application:

For deburring difficult to access areas, such as holes with cross-drilled bores

### Execution:

- Angled design
- Thermally insulated handle
- With speed control

### Advantage:

- Extremely quiet and robust
- Easy handling, especially for large workpieces
- Low air consumption, as drive is only applied during the work process



<b>Art. no.</b>	<b>75061 260</b>
<b>Brand</b>	MANNESMANN DEMAG
<b>Manufacturer Part Number</b>	29945645
<b>Model</b>	BSW 506
<b>Valve design</b>	Lever valve
<b>Max. idle speed</b>	500 rpm
<b>Power input</b>	65 W
<b>Air consumption</b>	5 l/s
<b>Suitable for bore diameter</b>	25 mm
<b>Length</b>	295 mm
<b>Head height</b>	30.5 mm
<b>Diameter of housing</b>	30 mm
<b>Weight</b>	0.85 kg
<b>Max. bore diameter</b>	25 mm
<b>Connection thread</b>	G 1/4 inch
<b>With speed control</b>	Yes
<b>Sound-pressure level</b>	71 dB
<b>Gross Weight</b>	1.612 kg
<b>Product Group</b>	7AA

### EAN

4251757300431