


Contact Points

Optional Accessories for Digimatic and Dial Indicators and Linear Gages

ø.118" (ø3mm) Ball point



4-48UNF


L	Carbide	Sapphire	Ruby	Plastic
.25"	21BZB005*	—	—	—
.28"	—	—	—	902018
.3"	131262	131263	131264	—
.6"	131265	131266	131267	—
1"	131268	131269	131270	—

M2.5 x 0.45mm

L	Carbide	Sapphire	Ruby	Plastic
7.3mm	901312*	—	—	901994
8mm	120045	120046	120047	—
15mm	120049	120050	120051	—
25mm	120053	120054	120055	—

*Furnished with standard metric dial indicators.

Shell point




4-48UNF

L	Order No.
3/32" (.094")	193697
5/32" (.156")	101184
1/4" (.25")	21AAA031
3/8" (.375")	21AAA032
1/2" (.5")	101185
5/8" (.625")	21AAA033
3/4" (.75")	101186
7/8" (.875")	21AAA034
1"	101187
1 1/4" (1.25")	21AAA035
1 1/2" (1.5")	21AAA036
1 3/4" (1.75")	21AAA037
2"	21AAA038
2 1/4" (2.25")	21AAA039
2 1/2" (2.5")	21AAA040
2 3/4" (2.75")	21AAA041
3"	21AAA042

M2.5 x 0.45mm

L	Order No.
5mm	101386
10mm	101118
15mm	137393
20mm	101387
25mm	101388
30mm	21AAA254


ø.16 Ball Point



4-48UNF

Order No.
21BZB005


ø1.8mm Ball Point



M2.5 x 0.45mm

Order No.
101122

Needle point




4-48UNF

L	Order No.	SR
.6"	21AAA030	.016"
1"	21AAA046	.016"
1 1/2"	21AAA047	.016"
2"	21AAA048	.016"

M2.5 x 0.45mm

L	Order No.	SR
15mm	101121	0.4
17mm	137413	0.2

Flat point




4-48UNF

D	L	Order No.
Ø1/2"	3/8"	101188
Ø3/8"	3/8"	101189

M2.5 x 0.45mm

D	L	Order No.
Ø10mm	10mm	101117

Flat-point, Carbide tip




4-48UNF

D	d	L	Order No.
Ø.2"	Ø.17"	.2"	131259
Ø.27"	Ø.25"	.4"	131260
Ø.41"	Ø.37"	.4"	131261

M2.5 x 0.45mm

D	d	L	Order No.
Ø5.2mm	Ø4.3mm	5mm	120041
Ø7mm	Ø6.5mm	10mm	120042
Ø10.5mm	Ø9.5mm	10mm	120043

Spherical-point, Carbide tip




4-48UNF

D	d	Radius	L	Order No.
Ø.2"	Ø.17"	.2"	.2"	131273
Ø.27"	Ø.16"	.16"	.4"	131274
Ø.41"	Ø.37"	.4"	.4"	131275

M2.5 x 0.45mm

D	d	Radius	L	Order No.
Ø5.2mm	Ø4.3mm	5mm	5mm	120058
Ø7mm	Ø6.5mm	7mm	10mm	120059
Ø10.5mm	Ø9.5mm	10mm	10mm	120060

Needle point, Carbide tipped




4-48UNF

D	L	Order No.
Ø.018"	.12"	131281
Ø.04"	.12"	131280
Ø.06"	.5"	131279
Ø.078"	.04"	131271

M2.5 x 0.45mm

D	L	Order No.
Ø0.45mm	2.5mm	120066
Ø1mm	2.5mm	120065
Ø1.5mm	13mm	120064
Ø2mm	1mm	120056
Ø2mm	8mm	137257

ø.2" (ø5mm) Flat point




4-48UNF

L	Order No.
5/16"	133017
1/2"	21AAA043
3/4"	21AAA044
1"	21AAA045

M2.5 x 0.45mm

L	Order No.
8mm	131365

Knife-edge point, Carbide tipped




4-48UNF

Order No.
131282

M2.5 x 0.45mm

Order No.
120067

Spherical point



4-48UNF

D	L	Radius	Order No.
Ø.5"	.125"	.28"	101205
Ø.375"	.09375"	.35"	101204


M2.5 x 0.45mm

D	L	Radius	Order No.
Ø10mm	5mm	7mm	101119

Contact Points

Optional Accessories for Digimatic and Dial Indicators and Linear Gages

60° Conical point




4-48UNF

M2.5 x 0.45mm

L	Order No.
1/2"	101190

L	Order No.
10mm	101120

90° Conical point




4-48UNF

M2.5 x 0.45mm

L	Order No.
1/4"	101191

L	Order No.
5mm	101385

Blade point, Carbide tip




4-48UNF

M2.5 x 0.45mm

D	T	Order No.	D	T	Order No.
.08"	.016"	131276	2mm	0.4mm	120061
.08"	.024"	131277	2mm	0.6mm	120062
.16"	.04"	131278	4mm	1mm	120063

90° Conical point, Carbide tipped



4-48UNF

4-48UNF

L	Order No.
.08"	131272

L	Order No.
.3"	131283


M2.5 x 0.45mm

M2.5 x 0.45mm

L	Order No.
2mm	120057

L	Order No.
8mm	120068

Roller Point




4-48UNF

M2.5 x 0.45mm

Order No.
901991

Order No.
901954

Extension Rod



4-48UNF


M2.5 x 0.45mm

L	Order No.
1/2"	139167
1"	301655
2"	301657
4"	301659


L	Order No.
10mm	303611
15mm	21AAA259A
20mm	303612
25mm	21AAA259B
30mm	303613
35mm	21AAA259C
40mm	21AAA259D
45mm	21AAA259E
50mm	21AAA259F
55mm	21AAA259G
60mm	304146
65mm	21AAA259H
70mm	21AAA259J
75mm	21AAA259L
80mm	21AAA259M
90mm	304147
100mm	303614

Point Conversion

M2.5 x 0.45mm 4-48 UNFI



4-48 UNFI M2.5 x 0.45mm




Order No.

21AAA011

Order No.

21AAA012

Lever Point



4-48UNF

M2.5 x 0.45mm

Order No.

900393

Order No.

900391

Interchangeable Contact Point Set (M2.5x0.45)

Set Order No. 7822



Individual No.	Description
131365	Flat Point (ø5mm)
101117	Flat Point (ø10mm)
101121	Needle Point
101119	Spherical Point
101118	Shell Type Point
101387	Shell Type Point