




SENKKOPF (100°) MIT GERILLEM NIETDORN COUNTERSUNK HEAD (100°) WITH GROOVED MANDREL TÊTE FRAISÉE (100°) CLOU CANNELÉ













Edelstahl A2 [1.4567]
Stainless steel A2 [AISI 302]
Acier inox A2 [1.4567]


Edelstahl A2 [1.4301]
Stainless steel A2 [AISI 304]
Acier inox A2 [1.4301]











Ø 4,8 mm

D1 = 4,8 + 0,08 / - 0,15 mm
D2 = 8,8 + / - 0,40 mm
k = 1,8 + / - 0,40 mm
d = 3,1 + 0,10 / - 0,10 mm
P = ≥ 30,0 mm
L = + 0,5 / - 0,2 mm
 4,9 - 5,1 mm

|  | F max |  |  |  |  |  |  |  |
|---|---------|---|--|---|---|---|---|---|
| 4,8 x 11,5 mm | 15,0 mm | 3,5 - 6,0 mm | 78404 48115 | 3500 N | 5100 N | 445 N |  |  |
| 4,8 x 14,0 mm | 17,5 mm | 6,0 - 8,5 mm | 78404 48140 | 4500 N | | | 250 | 2500 |
| 4,8 x 16,5 mm | 20,0 mm | 8,5 - 10,0 mm | 78404 48160 | 5500 N | | | 250 | 2500 |

Ø 6,4 mm

D1 = 6,4 + 0,08 / - 0,15 mm
D2 = 10,6 + / - 0,40 mm
k = 2,0 + / - 0,40 mm
d = 4,17 + 0,10 / - 0,10 mm
P = ≥ 32,0 mm
L = + 0,5 / - 0,2 mm
 6,5 - 6,7 mm

|  | F max |  |  |  |  |  |  |  |
|---|---------|---|--|---|---|---|---|---|
| 6,4 x 11,5 mm | 16,0 mm | 3,8 - 5,8 mm | 78404 64115 | 9100 N | 8000 N | 1112 N |  |  |
| 6,4 x 12,5 mm | 17,0 mm | 4,8 - 6,8 mm | 78404 64125 | 10100 N | | | 250 | 2500 |
| 6,4 x 13,5 mm | 18,0 mm | 5,8 - 7,8 mm | 78404 64135 | | | | 250 | 2500 |
| 6,4 x 15,5 mm | 20,0 mm | 7,8 - 9,8 mm | 78404 64155 | 11100 N | | | 250 | 2500 |
| 6,4 x 17,5 mm | 22,0 mm | 9,8 - 11,8 mm | 78404 64175 | | | | 250 | 2500 |
| 6,4 x 19,5 mm | 24,0 mm | 11,8 - 13,8 mm | 78404 64195 | | | | 250 | 2500 |
| 6,4 x 21,5 mm | 26,0 mm | 13,8 - 15,8 mm | 78404 64215 | | | | 250 | 2500 |
| 6,4 x 23,5 mm | 28,0 mm | 15,8 - 17,8 mm | 78404 64235 | 250 | | | 2500 | |

¹⁾ typische Werte typical values valeurs moyennes

Technische Änderungen vorbehalten Subject to technical modifications Sous réserve de modifications (techniques)