

## Product information

# 86 01 300

## Pliers Wrench

Pliers and a wrench in a single tool



- Replaces the need for sets of metric and imperial spanners
- Smooth jaws for damage free installation of plated fittings - working directly on chrome!
- Adjustable tightening tool
- Also excellent for gripping, holding, pressing and bending workpieces
- Push the button for adjustment on the workpiece
- Zero backlash jaw pressure prevents damage to edges of sensitive components
- Parallel jaws give a more solid grip; its design allows flexible adjustment of all widths up to the specified maximum size
- Reliable catching of the hinge bolt: no unintentional shifting
- The ratchet type principle allows quick and easy tightening and release of all bolted connections
- Lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened

### General

Article No.	86 01 300
EAN	4003773084662
Pliers	grey atramentized
Head	polished
Handles	with non-slip plastic coating
Weight	645 g
Dimensions	300 x 68 x 17 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Jaw thickness (joint) (B2)	9.5 mm
Joint thickness (B3)	15.0 mm
Tips thickness (B1)	9.5 mm
Adjustment positions	24
Capacities for nuts	Ø 2 1/2 Inch
Capacities for nuts	68 mm

technical change and errors excepted



