

90° conical countersink, HSS, for medium through hole

for universal use up to 1000 N/mm²

ORION[®]

Application:

For producing 90° counterbores of medium quality grade for through holes in accordance with DIN 74-1.

Execution:

- profile-ground with spiral blade

Advantage:

- spiral chip flutes ensure smooth cutting and the blade does not catch



Art. no.	11489 080
Brand	ORION
Manufacturer Part Number	11489080
Cutting material	HSS
Surface	Uncoated
Countersink angle	90 Degree
Tool holding device	HA parallel shank
Suitable for screw thread	M8
Spot-facer diameter	17.2 mm
Diameter of tenon	9 mm
Shank diameter	12.5 mm
Length	100 mm
DIN	1866
Gross Weight	0.100 kg
Product Group	103

EAN

4039247037032