

Shelf trolley with four two-part load areas, load capacity 300 kg

Load area 1280 x 315 mm, height 1530 mm

fetra
Transportgeräte

Application:

For the transportation and serving of small parts or other materials in Euro boxes.

Version:

- Steel tube/profile steel welded
- Variable screw-in shelves, 100 mm grid
- Steel frame with inserted wooden plate, surface beech decor, edge 12 mm high
- Infinitely adjustable inclination from 0° to 35°, secure locking by
- means of gripping screws

Art. no.	50268 438
Load-carrying capacity	300 kg
Loading surface size	1280 x 315 mm
Loading surface length	1280 mm
Loading-surface width	315 mm
Length	1420 mm
Width	740 mm
Height	1530 mm
Length x width x height	1420 x 740 x 1530 mm
Loading-surface height	370 mm
Loading-surface height 2	670 mm
Loading-surface height 3	970 mm
Loading-surface height 4	1270 mm
Wheel diameter	125 mm
Material of wheel	TPE
Wheel width	32 mm
Total stop optional	No



EAN-Code

4017976028910