

Product information


97 52 33

KNIPEX PreciForce® Crimping Pliers

- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Good handling thanks to favourable handle position, low weight, compact design and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened



General	
Article No.	97 52 33
EAN	4003773051862
Pliers	burnished
Handles	with multi-component grips
Weight	478 g
Dimensions	220 x 59 x 30 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details	
	
Application	non-insulated crimp terminals, tube and compression cable lugs in accordance with DIN 46234 and DIN 46235 and non-insulated crimp, butt and press connectors in accordance with DIN 46341 and DIN 46267
Capacity in square millimetres	0.5 — 10.0 mm ²
Number of crimping positions	4
AWG	20 — 8

technical change and errors excepted