

PCBN clamp holder, negative, right

For longitudinal turning using CN indexable insert

ATORN[®]

Application

For longitudinal turning using CN indexable insert 80°.

Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type C, 75° pitch angle, 80° tip angle, 0° clearance angle

Advantage

- extremely stable geometry for longitudinal machining with large feed depths and challenging conditions
- negative body geometry ensures good stability and absorption of force for large cutting depths



Art. No.	17837 115
ISO name	PCBN R/L 2525 M12
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	28 mm
Programming size	22 mm
Suitable for indexable inserts	CN.. 1204..
Tool design	Right
DIN	4983

EAN-Code

4050293127423