

Temperature-humidity measuring device

ORION®

Application:

For measuring indoor climates

Execution:

- Running display
- Max-hold display
- Min-hold display
- Energy-saving Auto-OFF function

Advantage:

- Handy device size and easy one-hand operation
- Automatic display illumination with brightness sensor
- Large digits for clear view of measured values

Delivery:

Battery (1x 9 V block battery, type 6 LR 61)



Art. no.	46210 010
Brand	ORION
Manufacturer Part Number	46210010
Min./max. temperature measuring range	-20 to 60 °C
Temperature error limit	0.5 °C
Min./max. humidity (rF) of measuring range	0-99 %
Humidity (rF) error limit/conditions	5 % / from 20 to 70%
Humidity (rF) error limit, residual area	7 %
Humidity (rF) error limit (+/-)	5 %
Number of rechargeable batteries/batteries	1 PCS
Gross Weight	0.209 kg
Conditions for humidity (rF) error limit	from 20 to 70%
Product Group	456

EAN

4039247962235