

## Datasheet

### About VP-R48G(869)

*VP-R48G(869) is an Android-based multimedia terminal with a 7 inch touch screen and a 1.3M CMOS sensor camera. It supports H.264/H.263 codecs with adaptive bandwidth adjustment. The 7" touch screen offers excellent user experiences such as high quality videophone, smooth internet surfing, various Android Apps and daily information.*



- 7 inch capacitive touch screen TFT LCD, 1024\*600 pixels;
- 1.3M pixels CMOS camera with privacy shutter;
- Dual switched 10/100/1000Mbps Ethernet ports, supporting IEEE802.11af and IEEE802.az Energy Efficient Ethernet;
- Built-in Bluetooth, USB and Wi-Fi feature;
- Built-in Radio Frequency Module: 869MHz;
- Android 5.1 Operating System and support Android API for the 3<sup>rd</sup> party Android application installation.
- Voice and Video Codec : PCMA,PCMU, G.722, G.723, G.729, H.263, H.264;
- Protocol: SIP RFC3261, TCP/UDP/IP, PPPoE, RTP/RTCP, HTTP/HTTPS, etc;
- AutoP: FTP/TFTP/HTTP/HTTPS

#### Video Features

- Video Codec: H.263,H.264
- Video Solution: QCIF, CIF, VGA, 4CIF, 720P
- Video Bitrate: 64kbps-2Mbps
- Adaptive Bandwidth Adjustment
- Video Character: PIP, Full Screen, Local Video ON/OFF Control
- Image Codec: JPEG, GIF, PNG, BMP

#### Audio Features

- Wideband Audio Codec: G.722
- Narrowband Audio Codec:PCMA,PCMU, G.723, G.729
- VAD
- CNG
- Echo Canceller G.165/G.168
- Full-Duplex Speakerphone
- 4 DTMF modes: RFC2833,In-Band, SIP INFO, Auto

#### Network and Security

- SIP V2(RFC3261)
- UDP/TCP/IP
- RTP/RTCP
- ARP/RARP
- NAT Traversal: Static NAT configure, SIP Keep Alive
- IP Assignment:Static IP, DHCP, PPPoE
- NTP For Auto Time Setting
- Network Packet Capture
- TFTP/FTP/HTTP/HTTPS Client API
- QoS: Layer 2 (802.1Q, 802.1p) and Layer 3 (ToS, DiffServ)
- HTTPS
- MD5 and MD5-sess Based Authentication
- Access for Administration

#### Phone Features

- Android 5.1 Operation System
- Support 6 SIP accounts
- Call Waiting
- Call Transfer
- Call Hold
- Mute
- Redial
- Speed Dial
- Direct IP call
- 6-Way Conference
- DND (Do Not Disturb)
- Volume Adjustable
- Ring Tones Selectable
- Multi-Languages Support
- Default Apps: Phonebook, Weather, Google Play, Digital Photo Frame, Stock, News Feeds, Calendar, World Clock, Alarm Clock, Email, Camera, File Browser Games.
- 3rd Party Android Applications

#### Directory

- Local Phonebook up to 3000 Groups
- Phonebook with Contact Picture
- Favorites
- Blacklist
- Call Logs: 600 Entries (200 Missed Calls; 200 Dialed Calls; 200 Received Calls.)
- LDAP
- Intelligent Search Method

#### Management

- Firmware Local Update:USB Flash Disk
- Firmware Remote Update: FTP method
- Auto Provisioning Using FTP/TFTP/HTTP/HTTPS
- System Log Export
- Restore To Factory Default
- Configuration Managements Via LCD

#### Physical Features

- 7 Inch Capacitive Touch Screen, Resolution 1024\*600, 16:9 Wide Screen Aspect Ratio
- 3 LED Lights (1 Power Light, 1 Network Light, and 1 Message Light)
- 28 Keys
- Flash Memory 8GB
- 2GB DDR3 Memory
- Foot Stand
- 1.3 Mega Pixels CMOS Camera, Free Rotation
- RJ9 Handset
- 3.5mm Headset jack
- 2 RJ45 10/100/1000M Ethernet Jacks
- Energy Efficient Ethernet: IEEE802.3az
- Power over Ethernet: IEEE802.3af
- 869MHz RF Module
- Bluetooth
- Wireless Access: 802.11b/g/n
- 1 USB 2.0
- 1 HDMI Video Out Port
- Power Adapter: AC 100~240V Input, DC 12V/1A Output
- Dimensions: 240\*192\*106mm
- Operating Temperature: 32° ~ 104°F (0° ~ 40°C)
- Storage Temperature: -4° ~ 158°F (-20 ~ 70°C)
- Operating Humidity: 10% to 90% Noncondensing
- Storage Humidity: 10% to 90% Noncondensing
- Power consumption (approx.): 12W
- Weight (approx.): 1.6kg
- Giftbox Size: 255\*198\*128mm

#### About Akuvox

Akuvox is a leading provider of HD IP Phone and Video Phone for SME, Enterprises and Carriers globally. With experienced R&D team in the field of VoIP and world-class STAR-NET's manufacturing facility, Akuvox produces competitive high quality products.

Akuvox provides excellent customer service with powerful technical support and partners all over the world. Our products have been deployed in more than 50 countries and well received by the customers.