

Data sheet

6GK1905-0AD00

Product type designation



Split Connect Terminator (Ex)

PROFIBUS PA SPLITCONNECT TERMINATOR (EX) FOR TERMINATING OF PROFIBUS PA SEGMENTS, SUIT. FOR APPLICATION IN EX-AREA, PACK. UNIT: 5 PIECES PER PACK

Electrical data

Transfer rate / with PROFIBUS PA	31.25 kbit/s
----------------------------------	--------------

Permitted ambient conditions

Ambient temperature / during operation	-40 ... +85 °C
Ambient temperature / during storage	-40 ... +85 °C
Ambient temperature / during transport	-40 ... +85 °C
Protection class IP	IP67

Further Information / Internet Links

Internet-Link

- to website: Selector SIMATIC NET
SELECTION TOOL
<http://www.siemens.com/snst>
- to website: Industrial communication
<http://www.siemens.com/simatic-net>
- to website: Industry Mall
<https://mall.industry.siemens.com>
- to website: Information and Download Center
<http://www.siemens.com/automation/net/catalog>
- to website: Image database
<http://automation.siemens.com/bilddb>
- to website: CAx Download Manager
<http://www.siemens.com/cax>
- to website: Industry Online Support
<https://support.industry.siemens.com>

last modified:

09.03.2015