

Taper Bush



Taper Bush Ref :

3020-40
3020 – Series
40mm – Bore Size

Specification	
Material Grade	GG25 Cast Iron
Keyway	BS Standard H7 Tolerances

Bush Size Series	1008	1108	1210	1610	1615	2012	2517	3020	3030	3525	3535	4030	4040	4535	4545	5040	5050
Screw Tightening Torque (Nm)	5.6	5.6	20	20	20	30	50	90	90	115	115	170	170	190	190	270	270
No of Screws	2	2	2	2	2	2	2	2	2	3	3	3	3	3	3	3	3
Hex Socket Size (mm)	3	3	5	5	5	6	6	8	8	10	10	12	12	14	14	14	14
Large End Diameter (mm)	35	38	47.5	57	57	70	85.5	108	108	127	127	146	146	162	162	178	178
Bush length (mm)	22.3	22.3	25.4	25.4	38.1	31.8	44.5	50.8	76.2	63.5	89	76.2	102	89	114	102	127
Approx Mass (Kg)	0.1	0.1	0.2	0.3	0.5	0.7	1.5	2.7	3.65	3.9	5.1	5.6	7.8	7.6	10	11.2	14

MECALINE V pulleys are all manufactured to the highest professional & quality standard - used widely in all aspects of industry. It's the Engineers preference by choice