

Electronic dial gauge

ID-S

Mitutoyo

Application:

for measuring lengths and differences in length, e.g. concentricity, flatness, position measurements.

Execution:

- ON/OFF
- Counting direction can be switched
- ABSOLUTE system for reliable measurement
- LCD digit size 9 mm
- Digimatic
- IP42

Advantage:

- Long battery life
- All functions can be adjusted via large and user-friendly keys



Art. no.	32019 358
Brand	MITUTOYO
Manufacturer Part Number	543-792
Length measuring range	12.7 mm
Digit increment	0.001 mm
Min./max. measurement force	0-1.5 N
Error limit	0.003 mm
Repeat accuracy	0.002 mm
Data transmission type	DIGIMATIC
IP protection class	IP 42
Functions	ABS function, On/Off, Reversal of counting direction
Absolute function	Yes
Automatic switch-off	No
Dynamic measurement	No
Preset function	No
Shank diameter	9.52 mm
Tolerance value entry	No
Manual tolerance markers	No
Number of rechargeable batteries/batteries	1 PCS
Colour reading classification	No
Rechargeable battery/battery capacity	155 mAh
Battery voltage	1.55 V
Weight of rechargeable battery/battery	0.002 kg
Battery designation	1,5 V SR44
Rotating housing	No
Combined indicator for figure/scale reading	No
Reversible counting direction	Yes
Digit height	9 mm
Display	Digital
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	0.290 kg
Product Group	3MA

EAN

4946368631370