



# HSK cable glands for special applications

## HSK-XL

Metr.



**Material** Nickel plated brass

**Seal** Buna-N


**O-Ring** Buna-N

**Protection** IP 68

**Operating Temperature** -40 °C – 100 °C (-40 °F – 212 °F)

**Advice:**

- Other sealing material e.g. Silicone upon request
- Stainless steel on request



AG	$\varnothing$ mm	GL mm	H mm	 mm	Number
M 63 x 1,5	48-55	10	42	75	1.106.6375.50
M 75 x 1,5	48-55	15	42	80	1.106.7500.50
M 75 x 1,5	53-60	15	42	85	1.106.7500.51
M 80 x 2	58-65	15	42	90	1.106.8000.50
M 90 x 2	63-70	15	42	100	1.106.9000.50
M 90 x 2	68-75	15	52	100	1.106.9000.51
M 100 x 2	78-85	20	52	110	1.106.1000.50
M 100 x 2	73-80	20	52	110	1.106.1000.51
M 110 x 2	83-90	20	52	120	1.106.1100.51

➔ Accessories see page 71