

## TE Type T - Surface sensor

watertight, with wider measuring tip



### Application:

The waterproof and robust surface sensor with wider measuring tip is suitable for temperature measurements on flat surfaces.

### Execution:

- Sensor type: TE Type T
- Measuring range: -50 to +350 °C
- Accuracy:  $\pm 0.2^{\circ}\text{C}$  at -20 to +70 °C
- Accuracy: Class 1 (remaining measuring range)
- Response time: 30 s
- Length/diameter of probe/sensor tube: 115 mm/5 mm
- Length/diameter of probe/sensor tube tip: 50 mm/6 mm
- Product/housing material: ABS/TPE/PUR

### Delivery:

1 x waterproof surface sensor (TE Type T) with permanently connected cable (cable length 1.2 m).



<b>Art. no.</b>	<b>46108 130</b>
<b>Brand</b>	TESTO
<b>Manufacturer Part Number</b>	0603 1993
<b>Sensor type</b>	TE type T
<b>Probe type</b>	Surface probe
<b>Min./max. temperature measuring range</b>	-50 to 350 °C
<b>Accuracy temperature</b>	+/- 0.2 °C at -20 to +70 °C, Class 1 (remaining measuring range)
<b>Response time sensor</b>	30 s
<b>Diameter probe tube</b>	5 mm
<b>Diameter sensor tube tip</b>	6 mm
<b>Length sensor tube</b>	115 mm
<b>Length sensor tube tip</b>	50 mm
<b>Cable length</b>	1.2 m
<b>EN standard</b>	60584-1
<b>Material of housing</b>	ABS/TPE/PUR
<b>Gross Weight</b>	0.150 kg
<b>Product Group</b>	4CF

### EAN

4029547003912