




SSTGH040VASFPKG


Connection technology



Product characteristics

Wirable plug	
M12 connector	
wirable	
Gold-plated contacts	
Electrical data	
Electrical design	DC
Operating voltage [V]	10...55 DC
Current rating [A]	4; (...40 °C)
Environment	
Ambient temperature [°C]	-40...85
Protection	IP 67
Mechanical data	
Design	straight
Material body	PA
Material nut	stainless steel 316Ti / 1.4571
Weight [kg]	0.023
Electrical connection	
Connection	wirable; ...0.75 mm ² (Ø 4...6 mm)

Wiring



Remarks

Pack quantity	[piece]	1
---------------	---------	---