



RE014-LF

- SMD-Labcard
- Epoxy fibre-glass 1.50 mm
- Single-sided 35 µm Cu
- Hot air leveling (HAL-Leadfree)
- Solder stop mask
- 75 x 75 soldering pads 1.00 x 1.00 mm
- Hole spacing 1,27 x 1,27 mm
- Hole diameter 0.45 mm
- Size 99.06 x 99.69 mm




RE014-LF

- SMD-Laborkarte
- Epoxydglashartgewebe FR4 1,50 mm
- Einseitig 35 µm Cu
- Oberfläche HAL bleifrei
- Lötstopplack
- 75 x 75 Lötinseln 1,00 x 1,00 mm
- Raster 1,27 mm
- Lochdurchmesser 0,45 mm
- Größe 99,06 x 99,69 mm



RE014-LF

- Carte d'expérimentation SMD
- Fibre de verre époxyde 1.50 mm
- Simple face 35 µm Cu
- Étamée à chaud (HAL-sans plomb)
- Masque de soudure
- 75 x 75 îlots de brasage 1.00 x 1.00 mm
- Pas 1,27 x 1,27 mm
- Perforation 0.45 mm
- Dimensions 99.06 x 99.69 mm



RE014-LF

- Tarjeta experimental SMD
- Fibra de vidrio epoxídica FR4 1,50 mm
- Por un lado 35 µm de Cu
- Superficie HAL-leadfree
- Máscara de inhibidora de la soldadura
- 75 x 75 nodos de soldadura 1,00 x 1,00 mm
- Trama de agujeros 1,27 mm
- Diámetro de los agujeros 0,45 mm
- Tamaño 99,06 x 99,69 mm