

# Insafer HO Topper LED II 225

*Insafer HO Topper LED II 225 RO 25W WW*  
3033948



## Product features

- IP44 front round LED downlight with outputs of up to 2,289lm and an efficacy of up to 99lm/W. Polycarbonate diffuser with a white bezel. Shallow recess depth (<65mm). Available in 12, 15, 21 & 25W in 150mm, 175mm, 205mm & 225mm cut out sizes. Perfect for up to 2x26W CFL replacement. Includes loop-in loop-out facility for quick installation.




## PRODUCT OVERVIEW

Product name	Insafer HO Topper LED II 225 RO 25W WW
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality
ETIM Class	EC001744
E-number SE	7465636
Warranty	5 years
Fixture luminous flux (lm)	2071
Luminaire efficacy (lm/W)	83
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	74
Glare control	< 23
Photobiological Risk Group	RG0
Total power consumption (W)	25
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
LED Flickering Rate	Ultra low (5% or less)
Housing colour	RAL 9003 - Signal white
IP rating	IP44/20
IK rating	IK07
Product EAN number	8711971339489

## PHOTOMETRY

## Insaver HO Topper LED II 225

*Insaver HO Topper LED II 225 RO 25W WW*  
3033948



### TECHNICAL DRAWINGS

---

