

FEATURES

- **USB 3.0 SuperSpeed offering excellent transfer speeds**
- **USB 2.0, 1.1 compatible making it highly versatile**
- **Blue PVC sheath offering excellent durability and protection**
- **10 Pin**
- **28 AWG (American Wire Gauge)**
- **Overall Cable Diameter 5.0mm**
- **Shielded, Braided and Drain**
- **Gold contacts**
- **Nickel connectors with PVC hoods offering a reliable connection**

RS PRO Male USB A to Male USB B USB Cable, 5m

RS Stock No.: 182-8839



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This high quality USB cable from RS PRO features a USB 3.0 A male connector at one end and a USB 3.0 B male connector at the other, offering exceptional USB speeds and reliability suitable for a wide range of applications. With the addition of USB 3.0, the cable is also backwards compatible with USB 2.0 and 1.1, making it a highly versatile USB cable. The cable flex features copper wire conductors and drain wire with an aluminium braid for shielding, ensuring a high performance USB cable. The internal wires are enclosed in a blue PVC sheath offering excellent durability and corrosion resistance, whilst remaining flexible enough to accommodate cable management solutions. Both connector types are manufactured from nickel and feature PVC hoods, offering optimum performance and protection. This high performance USB cable is ideal for connecting various devices together that require charging, power or data to be transferred such as a computer and a printer.

General Specifications




USB Type	USB 3.0
Connector A	Male USB A
Connector A Type	USB A
Connector A Gender	Male
Connector B	Male USB B
Connector B Type	USB B
Connector B Gender	Male
Outer Sheath Material	PVC
Sheath Colour	Blue
Connector Plating	Nickel
Pin Construction	Nickel and also have PVC hoods
Applications	Printers, Scanners, External hard drives, Modems, Routers, Consoles, Audio and visual devices

Mechanical Specifications

Length	5m
---------------	----

Approvals

Standards Met	RoHS, CE, REACH
----------------------	-----------------



1. CABLE: UL2725,AL+B-FOIL,(30AWG*1P)+[AL+MY-FOIL,(30AWG*1P+D)]*2+24AWG*2C.
BLUE COLOR,OD=5.5mm,PVC JACKET.
2. LENGHT: 1.0M.
3. CONNECTORS: USB3.0 M(A)*1PCS,USBA 3.0M(B)*1(BLUE INSULATOR).
4. MOLD: MOLDING USB TYPE.
5. CONTACTS: WHITE/GREEN PAIR...30AWG , RED/BLACK...24AWG
6. OPEN/SHORT TEST: 100% TEST.
INSULATION: 2M.

