

## ToLEDo AVANT T8 CCG and AC

ToLEDo T8 V4 2FT 10W 1000LM 840

0027370

### Product features



- Energy efficient and affordable LED T8 solution to replace conventional fluorescent T8 lamps. Omnidirectional 320° uniform light distribution thanks to glass tube construction design, same as traditional fluorescent T8 tubes. High lumen package - 1000 lm/W. High lumen efficacy - 100 lm/W. Energy rating - A+. Switching cycles - 200,000X. Average life 40,000 hours lifespan (L70 F50). Wide beam angle - 220°. High power factor - 0.90. Suitable for general illumination in offices, supermarkets, department stores, train stations, petrol stations, parking lots and maintenance free applications. Suitable for operation with electromagnetic gears and direct mains operation (220-240V). 3-Year warranty.



### PRODUCT OVERVIEW

Product name	ToLEDo T8 V4 2FT 10W 1000LM 840
Technology	LED
Watt (Rated) (W)	10
Lamp shape	Tube, double-ended
Cap/Base	G13
Lamp finish	Frosted/Coated
General application	Logistics & Industry, Education, Residential & Consumer, Office, Hospitality, Retail, Museums & Galleries
ETIM Class	EC001959
E-number FI	4740442
E-number SE	8292185
Warranty	3 years
Luminous flux (lm)	1000
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	840
CRI (Ra)	80
Colour Consistency (SDCM)	6
Wattage (W)	10
Product Voltage (V)	4
Dimmable	No
Average life (Nominal) (h)	40000
IP rating	IP20
Product EAN number	5410288273709

### DATA TABLE

#### General data

Product name	ToLEDo T8 V4 2FT 10W 1000LM 840
Technology	LED
Watt (Rated) (W)	10
Lamp shape	Tube, double-ended
Cap/Base	G13
Lamp finish	Frosted/Coated

## ToLEDo AVANT T8 CCG and AC

ToLEDo T8 V4 2FT 10W 1000LM 840

0027370

General application	Logistics & Industry, Education, Residential & Consumer, Office, Hospitality, Retail, Museums & Galleries
ETIM Class	EC001959
E-number FI	4740442
E-number SE	8292185
Warranty	3 years

### Optical data

Luminous flux (lm)	1000
Luminous flux (Rated) (lm)	1000
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	840
CRI (Ra)	80
Colour Consistency (SDCM)	6
Adjustable chromaticity	N
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	10
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Current (A)	45
Mains voltage (V)	230V
Product Voltage (V)	4
Lamp power factor	0.9
Control gear required	No
No. Of switching cycles before premature failures	>200000
Transformer required	No
Dimmable	No
kWh per 1000 hours burning time	10

### Lifetime data

Average life (Nominal) (h)	40000
Average life (Rated) (h)	40000

### Physical data

IP rating	IP20
Nominal Product Length (mm)	603
Max. Length base to base (mm) - A	589
Length base to pin Min-Max (mm) - B	596
Max. Lamp Length (mm) - C/L	603
Max. Lamp Diameter (mm) - D	28
Weight (kg)	0.125

### Packaging

Single packaging type	Carton
-----------------------	--------

## ToLEDo AVANT T8 CCG and AC


ToLEDo T8 V4 2FT 10W 1000LM 840  
0027370

Product EAN number	5410288273709
Packaging single length / height (cm)	67.0
Packaging single width (cm)	4.6
Packaging single depth (cm)	4.6
DUN14 (outer)	15410288273706
Units per outer package	10
Packaging outer length / height (cm)	69.5
Packaging outer width (cm)	25.9
Packaging outer depth (cm)	12.2

### Safety data

Breakage cleaning instructions	Not applicable
Recommendation for disposal at end of life	Not Applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Suitable for accent lighting	Yes
Safety message	Suitable for totally enclosed fixture

## PHOTOMETRY



## TECHNICAL DRAWINGS

