

Product information

97 33 01

KNIPEX MultiCrimp®

Lever Action Crimping Pliers with changer magazine




- The crimping dies 97 49 xx for the Crimp System Pliers 97 43 200 are not compatible with the KNIPEX MultiCrimp 97 33 01/02
- Just one tool for the most common crimping applications
- Crimping dies changed quickly and easily without any additional tool
- Sorted and protected storage of the interchangeable dies in a round magazine
- Comfortable, powerful crimping pliers in professional quality
- Same reliable crimping results as with fixed crimping dies
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Special quality chrome vanadium electric steel, oil-hardened
- Round magazine: glass fibre reinforced plastic



General

Article No.	97 33 01
EAN	4003773066927
Pliers	burnished
Handles	with multi-component grips
Weight	770 g
Dimensions	250 x 75 x 28 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details



Application	non-insulated open plug type connectors (plug width 4.8 + 6.3 mm)
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimping positions	3
AWG	20 — 10

technical change and errors excepted



Changing the crimping dies: unlock the magazine position, take out the set of dies which the pliers have been pushed on



Changing position: service lever opens out for parallel jaw positioning



Fold in the service lever and press the pliers – ready for use again

