

## LED Bulb Series



### VT-215

#### HIGHLIGHTS :

WATTS



15

EQ. WATTS



85

LUMINOUS



1250

BEAM ANGLE



200

#### PRODUCT FEATURES

Item No	:	VT-215
SKU Code	:	159
Watts	:	15
EQ. Watts	:	85
Base / holder	:	E27
Voltage	:	AC:220-240V,50Hz
Lumen(lm)	:	1250
Color Temperature	:	3000K
Beam Angle	:	200
Commercial type	:	A65
PF	:	>0.5
LED Chip Type	:	SMD-Samsung Chip
CRI	:	>80
Energy rating label	:	A+
Certification	:	EMC,LVD,ROHS
IP Rating Protection Class	:	IP20
Body type	:	Thermoplastic
Dimmable	:	No
Life Time	:	30,000 Hours
Operation Temperature	:	-25 to +45°c
EAN code	:	3800157627726
Unit size	:	ø66.5x134mm
Packing details	:	100.00
Unit cbm	:	0.00080