


Waterproof Palm pH™ Meter

 **Big Digit LCD display in rugged housing**
With choice of stick or cabled pH Electrode

Features:

- Large LCD displays pH or mV and Temperature simultaneously
- Microprocessor provides for Automatic Buffer recognition
- Memory stores 25 readings
- Automatic Temperature Compensation via Pt-100 sensor built into electrode
- Unit is completely waterproof when electrode is connected to the meter
- Low Battery indicator and Auto Power off
- Rugged design for handheld or wall mount (magnetic back)
- Specifically designed for fast response measurement
- Complete with waterproof meter, pH electrode, protective holster, pH 4 & 7 buffers (1 pouch ea.), and 9V battery
- **Select PH220-C** Kit to include ATC pH polycarbonate electrode (12mm diameter) with 39" (1m) cable
- **Select PH220-S** Kit to include ATC pH stick type polycarbonate electrode (12mm diameter) for direct connection to meter



Specifications	Model PH220-C	Model PH220-S
Type	Cabled pH Electrode	Stick pH Electrode
pH		0.00 to 14.00pH
mV		-999 to 999mV
Temperature		32 to 212°F (0 to 99.9°C)
Resolution		0.01pH, 1mV, 0.1°
Accuracy		±0.01pH, ±2mV, ±0.8°F/±0.5°C
Dimensions		4.4 x 3.1 x 1.5" (111 x 79 x 39mm)
Weight		9.2oz (260g)

Ordering Information:

- PH220-CWaterproof Palm pH Meter with cabled pH electrode
 PH220-SWaterproof Palm pH Meter with stick pH electrode
 6015WCWaterproof pH electrode with cable for Palm pH Meter
 6012WSWaterproof stick type pH electrode for Palm pH Meter
 PH103Tripak buffer pouches (6ea. 4, 7, 10pH, 2 Rinse solution)
 650470Tripak buffer capsules (3 vials - 10ea. of 4, 7, 10pH)

