

T150LL9X2



Article Number: 111-15719

Heavy Duty Cable Tie, 36.4" Long, 175 lb Tensile Strength, PA66, Natural, 25/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number T150LL9X2

Type T150LL

Color Natural (NA)

Features and Benefits

- Heavy duty design to offer higher tensile strength.
- Head design provides high tensile strength with very low insertion force.

Product Description HellermannTyton heavy duty cable ties offer a higher tensile strength for heavy load applications. The head design guarantees high tensile strength, as well as a low insertion force. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Heavy Duty Cable Tie, 36.4" Long, 175 lb Tensile Strength, PA66, Natural, 25/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 175.0 lbs

Minimum Tensile Strength (Metric) 780.0 N

Length L (Imperial) 36.4 "

Length L (Metric) 925.0 mm

Fixation Method None

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.35 "

Width W (Metric) 8.8 mm

Bundle Diameter Min. (Imperial) 0.32 "

Bundle Diameter Min. (Metric) 8.0 mm

Bundle Diameter Max. (Imperial) 10.8 "

Bundle Diameter Max. (Metric) 275.0 mm

Thickness T (Imperial) 0.079 "

Thickness T (Metric) 2 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 25 Pieces

Carton Quantity 500

Weight (Metric) 18.4 kg

Material and Specifications

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL94 V2
Halogenfree	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	Yes