



LED E14 T15X54 24V AC/DC 2.3W (20W) 200lm 829

Article number 80100038460

BAI LED Compact E14 Tube 15x54mm 24V AC/DC 180mA 0.18A 2.3W 2900K 200lm (20W) 20000h Indication- and signalling lamp

Compact and powerful LED indication & signaling lamp to replace the conventional miniature lamps. Not suitable for signal columns.



General ETIM properties

ETIM group	Lamps
ETIM class	Indication- and signalling lamp
Name	80100038460
Brand	Bailey
Productseries	LED Compact
Product type	Tube E14 LV

ETIM specifications

Energy efficiency class	G
Average nominal lifespan [h]	20000
Nominal current [mA]	180
Suitable for round flashing luminaire	No
Suitable for pointer	No
Suitable for torches	No
Total length [mm]	54
Diameter [mm]	15
Colour temperature [K]	2900
Colour	White
Xenon	No
Krypton	No
Halogen	No
Lamp shape	Tube, single-ended
Technology	LED
Socket	E14
Luminous flux [lm]	200
Lamp voltage [V]	24 - 24
Lamp power [W]	2.3 - 2.3

Alternative articles



80100040587

LED E14 T15X48
24-28V AC/DC 2.4W
(19W) 180lm 830