



# Wire and Cable Marking Labels



B-437 Yellow Tedlar in aerospace applications provides permanent identification of wire bundles.




Identifying flat ribbon and multi-paired colour cable is fast and easy with legends this sharp.



## B-437 Self-Extinguishing White or Yellow Tedlar® Film For cable marking


Order Reference	Pieces per Pack	Labels per Row	Label Width (mm) A	Label Height (mm) B	Horizontal Repeat (mm) C	Vertical Repeat (mm) D	Web Width (mm) E	Recommended Ribbon Series	IP™ Enabled/Compatible
THT-21-437	1	1	76.20	91.44	—	91.44	81.28	R-4300	IPE
THT-21-437-YL	1	1	76.20	91.44	—	91.44	81.28	R-4300	IPE

## B-427 Self-laminating Vinyl For flat ribbon cable marking.



Order Reference	Pieces per Pack	Labels per Row	Label Width (mm) A	Label Height (mm) B	Write-On Height (mm) C	Horizontal Repeat (mm) D	Vertical Repeat (mm) E	Web Width (mm) F	Recommended Ribbon Series	Max. Wire Diam (mm)	IP™ Enabled/Compatible
THT-10-427-3	3 000	3	25.40	95.25	25.40	27.30	101.60	85.09	R-4300	22	IPE
THT-10-427-3-YL	3 000	3	25.40	95.25	25.40	27.30	101.60	85.09	R-4300	22	IPE
THT-27-427-3	1 000	—	50.80	95.25	25.40	—	101.60	55.88	R-4300	22	IPE

## B-427 White or Yellow/Transparent Self-laminating Vinyl For wire and cable identification.



Order Reference	Pieces per Pack	Labels per Row	Label Width (mm) A	Label Height (mm) B	Write-On Height (mm) C	Horizontal Repeat (mm) D	Vertical Repeat (mm) E	Web Width (mm) F	Recommended Ribbon Series	Max. Wire Diam (mm)	IP™ Enabled/Compatible
● THT-8-427-10	10 000	5	12.70	36.50	12.70	16.81	41.28	85.09	R-4300	7	IPE
● THT-9-427-10	10 000	3	25.40	36.50	12.70	27.30	41.28	85.09	R-4300	7	IPE
● THT-9-427-10-YL	10 000	3	25.40	36.50	12.70	27.30	41.28	85.09	R-4300	7	—
● THT-10-427-3	3 000	3	25.40	95.25	25.40	27.30	101.60	85.09	R-4300	22	IPE
● THT-10-427-10-YL	3 000	3	25.40	95.25	25.40	27.30	101.60	85.09	R-4300	22	IPE
● THT-26-427-1	1 000	1	63.50	57.15	19.05	—	61.93	68.58	R-4300	12	IPE
● THT-27-427-1	1 000	1	50.80	95.25	25.40	—	101.60	55.88	R-4300	22	IPE
● THT-56-427-10	10 000	4	19.05	23.81	9.52	20.32	28.58	85.09	R-4300	4	IPE
▲ THT-61-427-5	5 000	1	36.50	12.70	12.70	—	17.45	41.58	R-4300	7	IPE
▲ THT-62-427-3.5	3 500	1	44.45	19.05	12.70	—	23.80	49.53	R-4300	10	IPE
▲ THT-63-427-3.5	3 500	1	36.50	20.32	12.70	—	25.07	41.58	R-4300	7	IPE
▲ THT-64-427-3.5	3 000	1	57.15	25.40	19.05	—	30.15	62.23	R-4300	12	IPE
▲ THT-64-427-3-YL	3 000	1	57.15	25.40	19.05	—	30.15	62.23	R-4300	12	—
▲ THT-65-427-3	3 000	1	95.25	25.40	25.40	—	30.15	100.33	R-4300	22	IPE
▲ THT-65-427-3-YL	3 000	1	95.25	25.40	25.40	—	30.15	100.33	R-4300	22	—
▲ THT-66-427-1.5	1 500	1	80.95	48.26	19.05	—	54.61	86.03	R-4300	19	IPE
▲ THT-67-427-1.5	1 500	1	57.15	50.80	19.05	—	55.55	62.23	R-4300	12	IPE
▲ THT-73-427-10	10 000	4	19.05	44.45	12.70	20.32	47.63	85.09	R-4300	10	IPE
▲ THT-74-427-10	10 000	4	20.32	36.50	12.70	20.32	41.28	85.09	R-4300	7	IPE
▲ THT-75-427-3	3 000	2	25.40	57.15	19.05	27.94	60.33	58.42	R-4300	12	IPE
▲ THT-75-427-3-YL	3 000	2	25.40	57.15	19.05	27.94	60.33	58.42	R-4300	12	IPE
▲ THT-80-427-5	5 000	4	12.70	19.05	9.53	15.24	24.13	63.50	R-4300	3	IPE
▲ THT-81-427-1	1 000	2	25.40	152.40	38.10	27.94	157.15	55.88	R-4300	36	IPE
▲ THT-82-427-1	1 000	1	50.80	152.40	38.10	—	158.75	55.88	R-4300	40	IPE
▲ THT-83-427-0.5	500	1	50.80	177.80	38.10	—	182.55	55.88	R-4300	44	IPE
▲ THT-85-427-2	2 000	1	50.80	152.40	38.10	55.88	157.48	R-4300	R-4300	36	IPE
▲ THT-86-427-2	2 000	1	50.80	177.80	38.10	55.88	182.88	R-4300	R-4300	44	IPE

Perforations exist between each row of labels for easy tear-off.