



Standard Industrial Cable Tie, 140X3.6mm, Natural, Indoor, 100PK

Basic data:

ID	0000460045
GTIN	7630268403041



Features:

These nylon cable ties are designed to withstand rough installation practices that occur in MRO and construction projects. They also help to provide superior bundle tightness, excellent tensile strength, and flexibility. Recommended for bundling wire, cable, or hose

Technical data:

Band width:	3.6 mm
Length belt/tape/tie:	140 mm
Tie thickness:	1.25 mm
Max. bundle diameter:	33 mm
Min. bundle diameter:	3.5 mm
Min. tensile strength:	180 N
Operating temperature:	-40 ... 85 °C
Mounting temperature:	-20 ... 85 °C
Model:	Internal toothed
Band closure:	Plastic lip/-cam
Material:	Plastic
Material quality:	Polyamide (PA)
Surface protection:	Untreated
Halogen free:	Yes
Colour:	White
Text strip:	None
Type of fastening:	None
UL approval:	Yes
Inflammability class of insulation material according to UL94:	V2