



# Precision pressure gauge MAP-40-4-1/8-EN

FESTO

Part number: 162842



## Data sheet

Feature	Value
Display range	0 bar ... 4 bar
Type code	MAP
Symbol	00991463
Conforms to standard	EN 837-1
Pressure gauge nominal size	40
Explosion prevention and protection	Zone 2 (ATEX) Zone 21 (ATEX) Observe the information on the certificate Zone 1 (ATEX) Zone 22 (ATEX)
Design	Bourdon tube pressure gauge
Type of mounting	Line installation
Operating medium	Neutral liquids Inert gas
Operating pressure	0 bar ... 4 bar
Intermittent load factor	0.66
Measurement accuracy class	1.6
Degree of protection	IP43
Temperature of medium	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 60 °C
Note on materials	RoHS-compliant
Connection position	Centered on rear side
Pneumatic connection	R1/8
Materials in contact with the media	Brass
Material of screwed trunnion	Brass
Housing material	PBT
Inspection window material	PS
Housing colour	Black
Product weight	60 g
Information on operating and pilot media	No oxygen No acetylene