


Nutensteine kugelgefedert,
einschwenkbar

Stahl blau verzinkt

Material-Nr	L10483-0504	L10484-0505	L10477-0604	L10477-0605	L10477-0606	L10478-0804	L10478-0805	L10478-0806	L10478-0808
	Nut 5		Nut 6			Nut 8			
M	M4	M5	M4	M5	M6	M4	M5	M6	M8
H, mm	4,65		6,3			7,7			
Hmax, mm	5,5		7,3			9,2			
L, mm	12		17,3			21			
B, mm	7,7		10,5			13			
b, mm	5		6,0			7,8			
Kompatibel mit Typ „I“, Raster	20 mm		30mm			40mm			



Material-Nr	L10482-0603	L10482-0604	L10482-0605	L10482-0606	L10479-1004	L10479-1005	L10479-1006	L10479-1008
	Nut 6				Nut 10			
M	M3	M4	M5	M6	M4	M5	M6	M8
H, mm	4,3				7,4			
Hmax, mm	5,1				9,1			
L, mm	14				22			
B, mm	8,0				16			
b, mm	6,0				9,8			
Kompatibel mit Typ „B“, Raster	20mm				40,45,50,60 In den leichten Ausführungen			

