


Schaltertype / Switch type: RLT180/3K4/Z20

Reparaturschalter / Maintenance switch 180A, 3 polig
Gehäuse / Box 373x373x230,
Griff absperbar / padlockable handle,

U_e
I_{th}
AC23 (400V)
AC3 (400V)
Anschlussquerschnitt max / Connection cross
Drehmoment Klemmen / Torque clamps

690VAC
180A
90kW
75kW
185mm²
10Nm

Durchbrüche / Knockouts 2xM40/63 2xM32/50 4xM25/40



DETAIL A
MAßSTAB 1 : 2