

## J.24 J - 3/8" metric 12-point sockets



### Description:

- OGV® profile: more powerful tightening, preserves fasteners.
- Finish: bright chrome.

A [mm]:	24
d [mm]:	26,3
d1 [mm]:	31,3
L [mm]:	33
L1 [mm]:	16,5
12-Point [mm]:	12
[g]:	86

