

Supplier's name or trade mark:		Beko		
Supplier's address :		Arctic S.A Gaesti, Dambovita, 13 Decembrie Street, No 210, Romania		
Model identifier:		WM310 7175746700		
General product parameters:				
Parameter	Value	Parameter	Value	
Rated capacity (kg)	7,0	Dimensions in cm	Height	84
			Width	60
			Depth	55
Energy efficiency index (EEI _w)	51,5	Energy efficiency class	A	
Washing efficiency index	1,035	Rinsing effectiveness (g/kg)	4,9	
Energy consumption in kWh per cycle, based on the eco 40-60 programme at a combination of full and partial loads. Actual energy consumption will depend on how the appliance is used.	0,444	Water consumption in litre per cycle, based on the eco 40-60 programme at a combination of full and partial loads. Actual water consumption will depend on how the appliance is used and on the hardness of the water.	45	
Maximum temperature inside the treated textile (°C)	Rated capacity	31	Weighted remaining moisture content (%)	53,9
	Half	27		
	Quarter	22		
Spin speed (rpm)	Rated capacity	1400	Spin-drying efficiency class	B
	Half	1400		
	Quarter	1400		
Programme duration (h:min)	Rated capacity	3:27	Type	Free-Standing
	Half	2:41		
	Quarter	2:41		
Airborne acoustical noise emissions in the spinning phase (dB(A) re 1 pW)	72	Airborne acoustical noise emission class (spinning phase)	A	
Off-mode (W) (if applicable)	0,50	Standby mode (W) (if applicable)	0,50	
Delay start (W) (if applicable)	4,00	Networked standby (W) (if applicable)	2,00	
Minimum duration of the guarantee offered by the supplier :		24 months		
This product has been designed to release silver ions during the washing cycle		NO		
Additional information:				
Weblink to the supplier's website, where the information in point 9 of Annex II to Commission Regulation (EU) 2019/2023 is found: http://support.beko.com				