

Electronic dial gauge

ID-H, CEE AC adapter

Mitutoyo

Application:

for measuring lengths and differences in length, e.g. concentricity, flatness, position measurements.

Execution:

- Preset function
- Data output via Digimatic and RS-232C
- LCD digit size 9.5 mm
- LOCK function (key lock)
- Counting direction can be switched
- MAX/MIN/MAX-MIN function

Advantage:

- Bi-colour tolerance monitoring
- High accuracy



Art. no.	32019 300
Brand	MITUTOYO
Manufacturer Part Number	543-563D
Length measuring range	60.9 mm
Digit increment	0.001 mm
Min./max. measurement force	0-2.5 N
Error limit	0.0025 mm
Data transmission type	DIGIMATIC
Functions	Reset (Zeroing the display), On/Off, Hold-function (AE lock), Preset function, Reversal of counting direction
Absolute function	No
Automatic switch-off	No
Dynamic measurement	No
Preset function	Yes
Shank diameter	8 mm
Tolerance value entry	Yes
Manual tolerance markers	No
Number of rechargeable batteries/batteries	0
Colour reading classification	No
Rotating housing	No
Combined indicator for figure/scale reading	Yes
Reversible counting direction	Yes
Digit height	9.5 mm
Display	Digital
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	1.165 kg
Product Group	3MA

EAN

494636850046 1