

Electronic dial gauge

MarCator 1086 R



Application:

For static measurements of lengths and length differences

Execution:

- Factor adjustable
- Large LCD display (11 mm)
- mm/inch switch-over
- LOCK function (key lock)
- Permissible deviation MPEp for increment 0.0005=2 µm, for increment 0.01=20 µm

Delivery:

In case with CR 2450 battery



Art. no.	33166 825
Brand	MAHR
Manufacturer Part Number	4337623
Length measuring range	100 mm
Digit increment	0.0005 mm
Min./max. measurement force	1.6-3.5 N
Error limit	8 µm
Repeat accuracy	1 µm
Data transmission type	multiCOM
IP protection class	IP 42
Absolute function	Yes
Automatic switch-off	Yes
Preset function	Yes
Tolerance value entry	Yes
Number of rechargeable batteries/batteries	1 PCS
Rechargeable battery/battery capacity	540 mAh
Battery voltage	3 V
Weight of rechargeable battery/battery	0.0059 kg
Battery designation	3V CR2450N lithium
Rotating housing	Yes
Reversible counting direction	Yes
Calibration Group Description	Dial gauge
Calibration Group	CE
Gross Weight	0.472 kg
Product Group	305

EAN

4059192014520