

Technisches Datenblatt / technical data sheet ratioform

				Toleranz	RS20	RS22	RS30	RS40
Farbe	color				transp./ clear	transp./ clear	transp./ clear	schwarz/ black
Länge	length		m	± 3%	300	300	300	300
Breite	Width		mm	± 3%	500	500	500	500
Dicke	Thickness		µm	± 2µm	17	20	23	23
Rollengewicht	weight per roll		kg	± 3%	2,7	3,1	3,5	3,5
Kerndurchmesser aussen	core diameter outside		mm	± 0,6mm	60	60	60	60
Kerngewicht	core weight		kg	± 5%	0,35	0,35	0,35	0,35
Rollen je Karton (weiß)	rolls per box (white)		St. / pcs.		6	6	6	6
Rollen je Palette	rolls per pallet		St. / pcs.		132	132	132	132
Garantierter Prestretch	guaranteed prestretch	ASTM D882 - 01	%	min.	50	60	70	70
Durchstoßfestigkeit	dart drop	ASTM D1709 - 01	g	± 10%	60	70	75	75
Klebkraft	Cling	ASTM D5458 - 95	g	± 10%	inside	inside	inside	inside

Stand 22.09.2013