

## Shoulder milling cutter VSM890™ with Weldon shank

For indexable milling inserts SN.X 1204..

**WIDIA** 

### Application:

The WIDIA™ Victory™ angular milling cutter range VSM890™-12 guarantees precise 90-degree shoulders and offers maximum economy with eight effective cutting edges per indexable insert. With an axial cutting depth of up to 8.0 mm, the tool also guarantees high productivity.

### Execution:

- Double-sided, robust indexable insert with 8 cutting edges
- Highly positive geometry for lower cutting forces
- Integrated facing chamfer for excellent surface quality
- Internal cooling

### Advantage:

- True 90° shoulders
- Cutting depths of up to 9.8 mm
- Low burr formation



<b>Art. no.</b>	<b>16044 200</b>
<b>Brand</b>	WIDIA
<b>Manufacturer Part Number</b>	6596066
<b>Cutting edge diameter</b>	32 mm
<b>Clearance length</b>	32 mm
<b>Length</b>	89 mm
<b>Shank diameter</b>	25 mm
<b>max. ap</b>	9.8 mm
<b>Number of cutting edges</b>	3 PCS
<b>Gross Weight</b>	0.312 kg
<b>Product Group</b>	1XJ

### EAN

4061779071673